

O & M

Bluetooth heaters with steel front

BEHA



Description of the bluetooth heater

Convactor heater with electronic thermostat intended for basic heating. This bluetooth heater has bluetooth technology which let you to control the heater with the Beha Bluetooth App, from a mobile phone or tablet when you are in the house. Beha bluetooth heater with, steel front, are IP24 tested and approved for installation in bathrooms and utility rooms. They can be installed according to current regulations.

After power outage the heater will use the last temperature set at the thermostat dial.

The heater has an open window detection. When opening the window, and the temperature in the room exceeds 15 degrees, the heater will shift between the set temperature and 5 degrees. This function is active for a maximum of 15 minutes.

The packaging is recyclable and should be disposed of in paper containers for cardboard.

Electrical connection and use

Before connecting, please ensure that the voltage is 230V AC 50Hz. The heater should be connected to the electrical socket in the room where it is intended to be used. Do not connect the heater with an extension cable as this may cause a fire hazard.

Care and Maintenance

Turn the thermostat dial to minimum temperature and turn the switch off. Remove the cord from the socket by gripping the plug and gently pulling it out of the wall socket. Make sure the heater is cooled down before cleaning.

Clean the outside with a damp cloth. Never use abrasive cleaners or submerge the heater into water or other liquids.

Vacuum behind and underneath the heater, twice a year. Before vacuuming released the wall bracket on top of the heater. On PB heater the two arms on the wall bracket are mounted in the T slot in the back plate. On LV heater the lower part, at the wall bracket, will hold the heater when vacuuming.

Other information

Defective heater must be delivered to a collection point for electrical waste. The heater must not be repaired, dismantled, or modified.

| Type | PB 4 | PB 6 | PB 8 | PB 10 | PB 12 | PB 15 | PB 20 | LB 5 | LB 7 | LB 10 | LB 12 |
|------------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| Item.no. | 820418 | 820420 | 850421 | 820422 | 820423 | 820424 | 820425 | 820620 | 820621 | 820622 | 820623 |
| Effect (W) | 400 | 600 | 800 | 1000 | 1250 | 1500 | 2000 | 500 | 750 | 1000 | 1250 |